


wellandable.com.au | thrive@wellandable.com.au | 07 3448 0446

Appendix 1: Colours and transfer patterns for Danmar Helmets

Custom Colours




Transfer Patterns





wellandable.com.au | thrive@wellandable.com.au | 07 3448 0446

Appendix 2: Customizations for Danmar Soft Shell Helmets



3469 QUICK-RELEASE BUCKLE CHINSTRAP

Designed for use in place of a standard chinstrap when frequent attempts to remove the helmet may occur. To release, simply squeeze the buckle. It is permanently attached to the helmet to prevent it from being removed or misplaced; you may choose either an Under the Chin closure or Top of the Helmet closure. Specify: Under the Chin or Top of the Helmet Closure.

3472 CUSTOM STRAPPING SYSTEM

Ideal for those situations where there are attempts to remove the helmet at inappropriate times. The straps are attached to each side of the helmet. They cross comfortably underneath the chin, and must cross once again in the back before finally attaching to the rear top of the helmet with Quick-Release Buckles.

*D-Rings or Metal Clips are available for added durability.





3467 REINFORCED SEAMS

We bond a strong reinforcement material into our foam liner seams to provide extra strength to these areas which may receive excess wear and tear.

3466 FOAM REINFORCEMENT

Reinforced vinyl material is bonded to the outer foam prior to being coated with vinyl to provide extra strength to a helmet which may receive excess wear and tear.




wellandable.com.au | thrive@wellandable.com.au | 07 3448 0446

Appendix 2: Customizations for Danmar Soft Shell Helmets



3471 PONYTAIL CUTOUT

A hole is cut into the rear top of the helmet to allow room for a ponytail.




3460 SOFT FOAM EAR COVERINGS

Fabricated from soft foam, these ventilated ear coverings extend down over the ears of our soft foam helmets



3468 FOAM VISOR

A thick 2" foam visor extends from the helmet approximately 3" and absorbs impact from bumps to the frontal area of head. Our closed-cell foam with vinyl-coating retains its compression resistance.



3464 REAR FOAM EXTENSION


In order to provide additional protection for the rear of the head, the vinyl-coated, shockabsorbing foam can be extended lower.

Specify: Length of extension when ordering.



wellandable.com.au | thrive@wellandable.com.au | 07 3448 0446

Appendix 2: Customizations for Danmar Soft Shell Helmets



3470 EYEGLASS RELIEF AREA

Eyeglasses can prevent a helmet from being properly positioned on a user's head. This modification of the Soft Shell Helmets incorporates a cut out which keeps the foam above the eyeglass level at the temples, ensuring that the helmet will not be pushed up on eyeglass frames. On the Hard Shell Helmets we substitute padded polypropylene slings, specially designed to allow extra room for eyeglass frames. This option can also be used to prevent breakage of the rubber ear slings on Hard Shell Helmets for individuals who tug at their ear slings and/or chinstraps.